



# CHEMRAZ<sup>®</sup>

Superior Chemical Resistance

Chemraz<sup>®</sup> Perfluoroelastomers



## THE VALUE OF CHEMRAZ®

Greene, Tweed partners with customers to provide reliable, efficient answers to their application needs. As a world-class leader in high-performance materials and engineering design skills, we leverage our expertise in a variety of markets and products to give our customers the most innovative and comprehensive solutions to their performance challenges. With our worldwide network of design engineers, Greene, Tweed delivers local technical expertise with a global reach.

### Industry Knowledge

Our industry knowledge coupled with our understanding of the design requirements, parameters and specifications enable us to develop both standard and custom solutions quickly and cost effectively. Our experience in demanding environments led us to the creation of Chemraz®, our innovative and most chemical-resistant elastomer.

### Broad Chemical Resistance

Greene, Tweed's Chemraz has the broadest chemical resistance of any elastomeric material, combining the resilience and sealing force of an elastomer with chemical resistance approaching that of PTFE. Chemraz O-rings, gaskets and custom elastomeric shapes extend MTBR (mean time between replacement) in harsh environments and withstand a wide range of temperatures (-20°F to 615°F, -30°C to 324°C).

Chemraz's distinctive chemical composition makes it well suited for a wide range of applications. Because of its low compression set, outstanding physical properties and universal chemical resistance, Chemraz provides an incredibly high sealing force. Chemraz extends the reliability and life of your equipment in hostile conditions while protecting people and the environment from emissions.

### Cost Effectiveness

Chemraz's unique property set and extended MTBR lowers customers' overall cost of operations. Versatile Chemraz seals work in almost all media, allowing our customers to use the same material in a variety of locations in one plant, lowering inventory control costs.

### Market Expertise

Greene, Tweed's extensive experience and knowledge of a variety of markets and products helps us create the best solution for each individual customer application. Our experience in several markets is particularly advantageous in the petrochemical and power generation industries. Because of our experience in the aerospace industry, we understand how to design seals capable of withstanding very close tolerances and exceptionally smooth surfaces, leading to reduced friction and wear while improving resistance to chemicals and minimizing extractables. Our experience in the semiconductor and pharmaceutical industries enables us to reduce contaminants through cleanroom environments.

### Engineering and Application Capabilities

With over one hundred years of experience, we have perfected techniques that ensure our customers receive the optimal solution to their performance challenges. Our application engineers are experienced in polymer specialties and equipped with the most up-to-date technology such as 3D modeling, 3D rapid prototyping and FEA capabilities. We partner with our customers—from collaboration on concepts through testing of prototypes to validation and production of finished parts. These close customer relationships give our customers the information they need to help them work with us throughout the decision-making process.

Chemraz components are available in standard shapes such as O-rings and gaskets, as well as in customer-specific designs, including flat seals, diaphragms, tubing, valve seats and rubber-to-metal connections.

### Assurance of Quality

Greene, Tweed adheres to the strictest of manufacturing standards. We are ISO 9001 certified, and we stand behind the quality and reliability of our products. Each product receives a bar code that carries a unique lot identification number verifying quality throughout the manufacturing process, from the compounding stage to the completed part.

Quality Inspection



Engineering Expertise



Industry Knowledge

**COMPETITIVE ADVANTAGE IN ANY ENVIRONMENT**

Because Chemraz® components withstand a broad spectrum of chemicals and temperatures, they perform well in an array of applications and environments.

**Petroleum Production**

Chemraz meets the critical requirements necessary for pumps, safety valves and other oilfield equipment. When RGD (rapid gas decompression) is a concern, we have specialty formulated material available.

**Chemicals and Hydrocarbon Processing**

Chemraz components offer universal chemical resistance, making them ideal for chemical and refining plants where aggressive chemicals are processed. Chemraz prolongs service intervals, enhances plant safety and protects the environment. Chemraz is ideal for a range of refining equipment, from mechanical seals and pump bodies to compressors and valves.

**Power Generation**

In modern power stations pressures to keep costs down and heightened environmental awareness demand greater efficiencies. At the same time, power station operators demand optimum reliability and extended periods of time between service intervals. Chemraz components help increase MTBR for a variety of applications, including pumps, valves and fittings in conventional and nuclear power stations and in nuclear fuel processing plants.

**Food and Pharmaceutical (FDA compliant)**

Products manufactured under the strictest regulatory standards, including FDA (U.S. Food and Drug Administration) and/or USP (United States Pharmacopoeia) Class VI, require components that provide unceasing reliability, feature total lot traceability, are fabricated using GMPs (good manufacturing practices) and contain minimal extractables. Components made from Chemraz deliver the safety and cleanliness demanding industries require.

**Biotechnology**


For the biotechnology market, reliability, safety, security and the ability to withstand extreme pressure and chemicals are paramount. Chemraz components provide resistance to a wide range of chemical solvents, extreme pressures and repeat sterilization. From HPLC and lab-on-a-chip to advanced laboratory and analytical equipment and solenoid valves, Greene, Tweed has experience meeting strict performance standards and design guidelines.

Chemicals and Refining

Oil and Gas



Power Generation



FDA Compliant



Biotechnology

HIGH-PERFORMANCE MATERIALS AT A GLANCE

Greene, Tweed's extensive portfolio of Chemraz® materials ensures customers the best compound available for each unique application.

**Chemraz 555, 605 and 600—broad chemical resistance**

Chemraz 555 offers broad chemical resistance in an extremely wide temperature range, outstanding physical properties and superior compression set resistance. Chemraz 605 and 600 provide the same chemical resistance as Chemraz 505 but with a higher temperature range.

Compound	555	605	600
Shore A Hardness	80	80	90
Temperature Range	10°F to 600°F (-12°C to 316°C)	-4°F to 500°F (-20°C to 260°C)	
Color	Black		



**Chemraz 505, 504 and 510—standard compounds**

Chemraz 505 offers broad chemical resistance for a wide range of applications. Chemraz 504 and 510 are softer and harder versions of Chemraz 505. Chemraz 504 is ideal for applications experiencing low forces, while Chemraz 510 is perfect for high-pressure applications.

Compound	505	504	510
Shore A Hardness	75	65	90
Temperature Range	-22°F to 446°F (-30°C to 230°C)		
Color	Black		



**Chemraz 615—for high temperatures**

Ideal for continuous high temperatures up to 615°F (324°C) because of its low compression set and outstanding mechanical properties.

Compound	615		
Shore A Hardness	80		
Temperature Range	0°F to 615°F (-18°C to 324°C)		
Color	Black		



**Chemraz 514 and 517—white compounds**

White compounds used wherever carbon black contamination must be avoided.

Compound	514	517
Shore A Hardness	70	80
Temperature Range	-20°F to 425°F (-29°C to 218°C)	
Color	White	



**Chemraz 584 and 585—specific media**

Ideal for use in strong oxidizing media and hot aqueous solutions.

Compound	584	585
Shore A Hardness	70	80
Temperature Range	-22°F to 428°F (-30°C to 220°C)	
Color	Cream	



**Chemraz SD625, SD517 and SD585—compliant compounds**

These specialty compounds are USP Class VI and FDA compliant. Additionally, SD625 and SD517 meet 3-A® Sanitary Standards.

Compound	SD625	SD517	SD585
Shore A Hardness	80	80	80
Temperature Range	-4°F to 500°F (-20°C to 260°C)	-22°F to 428°F (-30°C to 220°C)	
Color	Black	White	Cream



**Chemraz 526—rapid gas decompression resistant**

Rapid gas decompression resistant Chemraz with the same chemical resistance as Chemraz 505.

Compound	526		
Shore A Hardness	95		
Temperature Range	-4°F to 482°F (-20°C to 250°C)		
Color	Black		



## SPECIALTY COMPOUNDS FOR SPECIFIC REQUIREMENTS

Greene, Tweed's engineering experts work side by side with customers to find the best possible material and design for every application. The following sections highlight some specialty elastomers that were designed to meet the needs of specific challenging applications.

	FDA and USP Class VI Compliant	3-A® Sanitary Standards
Chemraz® SD625	X	X
Chemraz SD517	X	X
Chemraz SD585	X	

Compliance to U.S. FDA regulations is critical for those manufacturing products for the food or drug market. Greene, Tweed constantly strives to provide seal components that optimize both mechanical and physicochemical (absorption and extractables) performance. As a result, we do things for our customers that other companies are not able to offer. For complete and uncompromising solutions to pharmaceutical or hygienic fluid handling applications, only Greene, Tweed has virtual prototype and test capabilities in house. Our FEA design validations use mock-up equipment to deliver solutions that meet all your compliance needs in innovative ways.

At Greene, Tweed we take compliance seriously. Our reputation is built on the reputation of our customers. All of our compounded materials are third-party compliance tested. No matter what pharmaceutical or hygienic fluid handling process you are working with—or what part of the world you operate in—we deliver the most effective solution possible.

The FDA approves the use of food contact substances via the FCN process (Food Contact Substance Notification) described in Section 409(h) of the Federal Food, Drug and Cosmetic Act (21 U.S.C Section 348(h)). In publishing FCNs 000245 and 000247, the FDA confirmed that articles made from the Chemraz perfluoroelastomers SD625, SD517 and SD585 comply with the requirements for repeated use in contact with foods.

## Extraction Data

All extraction data has been determined by an independent certified test laboratory according to the prescriptions in the FDA paragraph 21 CFR, part 58 Good Laboratory Practice for Nonclinical Laboratory Studies:

- Total extractions according to 21 CFR 177.2400(d)(1)  
(0.2 mg/in<sup>2</sup> = 3,1 mg/dm<sup>2</sup>)
- Fluoride extractions according to 21 CFR 177.2400(d)(2)  
(0.03 mg/in<sup>2</sup> = 0,47 mg/dm<sup>2</sup>)

Parts made from these materials can be supplied with a certificate of conformity if required.

*Note: For perfluoroelastomers the very strict extractive limitations of FDA article 21CFR177.2400 Perfluorocarbon Cured Elastomers should always be applied. FDA article 21CFR177.2600 is effective for most of other elastomers like EPDM, FKM and NBR. FDA article 21CFR177.2400 has much stricter requirements for the total extractions, including limitations for fluorides. As a matter of course, Chemraz SD625, SD517 and SD585 fulfill the extraction limitations of the stricter article.*

## USP Class VI

The biocompatibility between a plastic or elastomer and a living organism is regulated with tests defined by the USP. Cytotoxicity is determined in the test tube (in vitro), while toxicity to the living organism is determined in the body (in vivo). Chemraz SD625, SD517 and SD585 are USP Plastic Class VI compliant; therefore, they are biocompatible.

Chemraz SD625 has also passed USP Physicochemical Testing <661> and has also been successfully tested to USP Elastomeric Closures <381>. This makes it the most comprehensively tested perfluoroelastomer for the food, drug and biomedical technology markets today.

## 3-A® Sanitary Standards

3-A SSI (3-A Sanitary Standards, Inc.) is a nonprofit organization serving the U.S. public health through the development of standards for the advancement of food sanitation and hygiene. Chemraz SD625 and SD517 have passed the 3-A Sanitary Standards for Multiple-Use Rubber and Rubber-Like Materials Used as Product Contact Surfaces in Dairy Equipment, Number 18-03, meaning these perfluoroelastomers meet strict hygienic criteria applicable to dairy equipment and systems.

Chemraz® SD625



Chemraz SD517




Chemraz SD585

### COMPRESSION SET

Generally, an elastomer's compression set is determined according to ASTM 395B. All tests are carried out in air at a temperature of 401°F (205°C) over 70 hours unless otherwise stated.

Compression set is as follows:



ASTM 395B states that compression set must be measured on a test body with a diameter of 1.14 in. (29 mm) and a thickness of .49 in. (12.5 mm). Although the value for compression set obtained by this method is very low, it is of little significance for parts used in the field. Greene, Tweed's data reflects the compression set obtained on O-rings of size -214 (.98 in. x .14 in./ 24.99 mm x 3.53 mm). These percentages are larger than those obtained on the test body but are more practical for the user.

The table below compares compression set measurements on three Chemraz® materials, first on the size -214 O-ring and second on the ASTM 395B test body, at otherwise identical conditions (70hr, air, 400°F/204°C). Depending on the particular material, the compression set measured in air can be very different from that measured in nitrogen. Chemraz materials deliver superior performance in a wide range of environments.

	With O-ring -214	With test body
Chemraz 505	25%	13%
Chemraz 510	30%	17%
Chemraz 605	20%	11%

### Resilience, Temperature Changes


Most methods for measuring compression set only measure resilience. They do not take into account the time taken by a seal to recover or its response to changes in temperature. Many dynamic applications, e.g., mechanical seals or quick-release couplings, require the rapid recovery of an elastomer for the safe functioning of a seal. Chemraz materials excel in these environments by delivering the type of rapid recovery usually associated with rubber.

### RAPID GAS DECOMPRESSION RESISTANT—CHEMRAZ® 526


The severe consequences of rapid gas decompression (also known as explosive decompression) occur in elastomers when there is a sudden drop in the pressure of gases, gas compounds or liquefied gases.

All elastomers are more or less permeable. When an elastomer is exposed to a high gas pressure for a certain length of time, it absorbs the gases that settle in the interstices between the elastomer's molecule chains. This process continues until the pressure inside the seal equals the pressure in the surrounding system. The higher the pressure, the more gas is absorbed. If the system depressurizes rapidly, the gas in the elastomer will expand under its own high pressure. If pressure cannot escape from the elastomer fast enough or if the elastomer's structure is not stable enough, bubbles or cracks will form, destroy the seal and lead to a loss of functionality. These problems will continue to occur hours after the drop in pressure. The seal's rapid increase in volume may also cause extrusion phenomena.

The photo below shows an O-ring that has been exposed to rapid depressurization in natural gas extraction at high pressure and high temperature. The ruptures and blisters caused by the sudden and rapid drop in pressure are visible.



Gases penetrating a seal



O-ring exposed to rapid depressurization

When RGD (rapid gas decompression) is an issue, consider the following when choosing an elastomer: type of gas, temperature, pressure (pressure level, pressure progression, rate of pressure drop) and seal material (hardness, polymer architecture, cross-section diameter and compression).

Components made from RGD resistant Chemraz 526 withstand the challenging conditions caused by the mix of high pressures and high temperatures. Chemraz 526 offers superior RGD properties, broader chemical compatibility and an improved low-temperature operating window. Its compression set delivers improved sealing and leak prevention unmatched by the leading competitive material. In addition, the hardness of RGD resistant Chemraz 526 significantly reduces the risk of gap extrusion.

# inside advantage

Greene, Tweed partners with customers to provide reliable, efficient answers to their application needs. As a world-class leader in the design and manufacture of high-performance materials and custom-engineered components, we leverage our expertise in a variety of markets and products to give our customers the most innovative and cost-effective solutions to their demanding applications.

## Contact Us

### Greene, Tweed Companies

Corporate Headquarters  
Kulpsville, PA, USA  
Tel: +1.215.256.9521  
Fax: +1.215.256.0189

PetroChem & Power  
Houston, TX, USA  
Tel: +1.281.821.2094  
Tel: +1.800.820.9005  
Fax: +1.281.821.2696

Greene, Tweed & Co., Limited  
Ruddington, Nottinghamshire, England  
Tel: +44 (0) 115.9315.777  
Fax: +44 (0) 115.9315.888

Greene, Tweed & Co France SAS  
Cergy-Pontoise, Cedex, France  
Tel: +33 (0) 1.30.73.54.44  
Fax: +33 (0) 1.30.73.45.75

Greene, Tweed & Co. GmbH  
Hofheim am Taunus, Germany  
Tel: +49 (0) 6192.929950  
Fax: +49 (0) 6192.900316

Greene, Tweed & Co. Italia S.r.l.  
Milan, Italy  
Tel: +39 (0) 2.21.05.17.1  
Fax: +39 (0) 2.21.05.17.30

Greene, Tweed & Co. Japan  
Tokyo, Japan  
Tel: +81 (0) 3.3454.3501  
Fax: +81 (0) 3.3454.1040

Greene, Tweed & Co., Korea Ltd.  
Seoul, Korea  
Tel: +82 (0) 2.566.5244  
Fax: +82 (0) 2.566.5288

Greene, Tweed & Co., Benelux B.V.  
Halsteren, Netherlands  
Tel: +31 (0) 164.612.123  
Fax: +31 (0) 164.610.030

Greene, Tweed & Co. Pte Ltd  
Singapore  
Tel: +65.6555.4828  
Fax: +65.6555.5393

Greene, Tweed & Co. Pte Ltd  
Taiwan  
Hsinchu, Taiwan ROC  
Tel: +886.3.516.9068  
Fax: +886.3.516.9069



[www.gtweed.com](http://www.gtweed.com)

*Statements and recommendations in this publication are based on our experience and knowledge of typical applications of this product and shall not constitute a guarantee of performance nor modify or alter our standard warranty applicable to such products.*

*All trademarks are property of their respective owners.  
Greene, Tweed is an Equal Opportunity Employer © 2008, Greene, Tweed*



11/08-UO-2.5M BR-US-PP-004



Printed on Recycled Paper